



Cross recessed raised countersunk head tapping screw Phillips DIN 7983 C-H Steel Zinc plated black passivated ST3,9X25MM

Article number	26450.039.025
Brand	-
UBB	950352502328
UNSPSC	31161507
EAN	8715492655950
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	25 mm
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Self tapping thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

NF	E25-657
ISO	7051 CH
DIN	7983 CH

Technical Specification

D (mm)	3.9
dk	7.5
f ≈	1.3
k ≈	2.3
L (mm)	25
No. cross recess	2
P	1.4

Technical Drawing

