

Thread rolling countersunk
head screw Steel Zinc plated
M3X6



Article number	26555.030.006
Brand	-
UBB	500649047049
UNSPSC	31162400
EAN	8717077253124
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	≈7500-1-NE Z
-----	--------------

Technical Specification

d-D	M3
dk (max.)	5.6
k (max.)	1.65
L (mm)	6
No. cross recess	1
P	0.5

Technical Drawing

