



Cross recessed raised countersunk head tapping screw Phillips DIN 7983 C-H Steel Zinc plated ST2,9X13MM

Article number	26700.029.013
Brand	-
UBB	950352123315
UNSPSC	31161507
EAN	8715492946300
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2.9 mm
Length	13 mm
Driving features	Phillips
Head shape	Countersunk oval head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-657
ISO	7051 CH
DIN	7983 CH

Technical Specification

D (mm)	2.9
dk	5.5
f ≈	0.9
k ≈	1.7
L (mm)	13
No. cross recess	1
P	1.1

Technical Drawing

