



Cross recessed raised cheese head thread cutting screw Phillips DIN 7516 AE-H Steel Zinc plated M3X6

Article number	27100.030.006
Brand	-
UBB	950352261669
UNSPSC	31161507
EAN	8715492950789
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Info

The predrill diameterter Drill \varnothing (H11) is a guideline for medium strength material. For soft or thin materials a smaller hole can be chosen, for hard or thick material a bigger hole may be chosen. It is recommended to select the exact diameter based on tests. The engagement depth should by no means exceed twice the nominal screw diameterter. Warning: electroplating of

Standards

DIN	7516-AE H
-----	-----------

FABORY these products may
cause hydrogen
embrittlement.

Technical Specification

d-D	M3
dk	5.6
Drill ø (H11)	2.7
k	2.4
L (mm)	6
No. cross recess	1
P	0.5

Technical Drawing

