



**Cross recessed raised
cheese head thread cutting
screw Phillips DIN 7516 AE-
H Steel Zinc plated M4X16**

Article number	27100.040.016
Brand	-
UBB	950352262402
UNSPSC	31161507
EAN	8715492950871
PKG. of 2000	Full Box Only

Technical Parameters

Diameter	M4
Length	16 mm
Driving features	Phillips
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Info The predrill
 diameter Drill ø
 (H11) is a guideline
 for medium strength
 material. For soft
 or thin materials a
 smaller hole can
 be chosen, for hard
 or thick material a
 bigger hole may
 be chosen. It is
 recommended to
 select the exact
 diameter based
 on tests. The
 engagement depth
 should by no means
 exceed twice the
 nominal screw
 diameter. Warning:
 electroplating of

Standards

DIN	7516-AE H
-----	-----------

these products may
cause hydrogen
embrittlement.

FABORY

Technical Specification

d-D	M4
dk	8
Drill ø (H11)	3.6
k	3.1
L (mm)	16
No. cross recess	2
P	0.7

Technical Drawing

