



VBA PLUS Cross recessed raised cheese head screws for chipboard Pozidriv Steel Zinc plated 3,5X35MM

Article number	29750.035.035
Brand	-
UBB	950350499808
UNSPSC	31161508
EAN	8715492960023
PKG. of 500	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	35 mm
Driving features	Pozidriv
Head shape	Raised cheese head
Material	Steel
Surface treatment	Zinc plated

Info	<p>All dimensions are guide values and may deviate dependent on the manufacturer. Specific features VBA PLUS screws for chipboard: The screw head is marked with an + which indicates that the VBA PLUS screw is, and will remain a quality screw. A deeper Pozidriv (Z) cross recess which practically eliminates "slipping out" of the tool. A saw-tooth shaped thread form which results in a lower turning moment, a higher</p>
------	---

Standards

tensile value and reduces deformation in the materials to be joined. Fully threaded to the point (point of application) which ensures immediate penetration (biting) of the screw thread, resulting in a 30% reduction of turning time. Warning: electro-galvanizing of these products may cause hydrogen embrittlement.

Technical Specification

D (mm)	3.5
dk (max.)	6.9
k (max.)	2.6
L (mm)	35
No. cross recess	2

Technical Drawing

