



## Brady Icon W017-TRI 100-PE 3PC

Article number	2K786878
Brand	-
UBB	500671781812
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

### Technical Parameters

Color	Black/Yellow
Width (mm)	100
Adhesive component	Permanent Acrylic
Basic material	Laminated Polyester
Brady material number	B-7541
Country	EMEA
Legend	ISO Safety Sign - Warning; Hot surface
Legend language	Global
Max. service temp. °C	110 °C
Min. service temp. °C	-40 °C
PIC description	Warning; Hot surface
Product regulations	ISO 7010
Sign type	Warning
Content (pcs)	3
Number of holes	0
Finish	Gloss
Finish	Glanz
Finish	luciu
Finish	Połysk
Finish	Brillo
Finish	Lesk

### Standards

Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & safety identification
Height (mm)	87
Length (L) (mm)	100
Thickness	0.099
Type nr.	B-7541
Weight (g)	9
Shape	Triangle

**UR COURSE**

BE THE STANDARD  
IN FASTENING SOLUTIONS