


MAXXFAST Universal woodscrew cross recessed countersunk head Steel Zinc plated 6X40MM (25)



Article number	30000.060.040
Brand	-
UBB	500512193979
UNSPSC	31161508
EAN	8715494279123
PKG. of 200	Full Box Only

Technical Parameters

Diameter	6 mm
Length	40 mm
Driving features	Pozidriv
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Info	Full boxes only. F = 9mm only if L ≥ 40mm. Diameters 3 and 3,5 are unfit for structural timber joints and therefore not CE marked.

Standards

Technical Specification

D (mm)	6
dk	12
F	9
k	6.3
L (mm)	40
No. cross recess	3
S	25

Technical Drawing

