



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Steel Zinc plated ST3,5X16MM

Article number	30300.035.016
Brand	-
UBB	500618323124
UNSPSC	31161507
EAN	8715494501736
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	16 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15482 H
DIN	≈7504-O H

Technical Specification

D (mm)	3.5
dk	6.9
k	2.35
L (mm)	16
L1	4
No. cross recess	2

Technical Drawing

