



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Steel Zinc plated ST3,9X25MM

Article number	30300.039.025
Brand	-
UBB	500618323959
UNSPSC	31161507
EAN	8715494501811
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	25 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Full boxes only.

Standards

DIN	≈7504-O H
ISO	≈15482 H

Technical Specification

D (mm)	3.9
dk	8
k	2.6
L (mm)	25
L1	4.5
No. cross recess	2

Technical Drawing

