



**MAXXFAST Self-drilling
screw countersunk head
cross recessed DIN ≈7504
O-H Stainless steel A2
ST3,5X22MM**

Article number	30305.035.022
Brand	-
UBB	500618326010
UNSPSC	31161507
EAN	8715494502023
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	22 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15482 H
DIN	≈7504-O H

Technical Specification

D (mm)	3.5
dk	6.9
k	2.35
L (mm)	22
L1	4
No. cross recess	2

Technical Drawing

