



MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O- H Bi-Metal ST3,5X19MM

Article number	30310.035.019
Brand	-
UBB	500618328586
UNSPSC	31161507
EAN	8715494502276
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.5 mm
Length	19 mm
Driving features	Phillips
Head shape	Countersunk head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15482 H
DIN	≈7504-O H

Technical Specification

D (mm)	3.5
dk	6.9
k	2.35
L (mm)	19
L1	4
No. cross recess	2

Technical Drawing

