

## MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O- H Bi-Metal ST3,5X25MM



Article number	30310.035.025
Brand	-
UBB	500618328743
UNSPSC	31161507
EAN	8715494502290
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (mm)	3.5
Length (L) (mm)	25
Driving features	Phillips
Head shape	Countersunk head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

### Standards

ISO	≈15482 H
DIN	≈7504 O-H

### Technical Specification

$d_k$	6,90 -7,30
k	2.35
$L_1$	4
No. cross recess	2

### Technical Drawing

