

MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O- H Bi-Metal ST4,2X16MM



Article number	30310.042.016
Brand	-
UBB	500618329246
UNSPSC	31161507
EAN	8715494502344
PKG. of 200	Full Box Only

Technical Parameters

Diameter (mm)	4.2
Length (L) (mm)	16
Driving features	Phillips
Head shape	Countersunk head
Material	Bi-Metal
Thread	Self tapping thread
Info	Full boxes only.

Standards

DIN	≈7504 O-H
ISO	≈15482 H

Technical Specification

d_k	8,00-8,40
k	2,6
L_1	5
No. cross recess	2

Technical Drawing

