

MAXXFAST Frame anchor nylon Plastic Nylon (polyamide) 8X80



Article number	30509.080.080
Brand	-
UBB	500619768533
UNSPSC	31162400
EAN	8715494127714
PKG. of 50	Full Box Only

Technical Parameters

Length	75 mm
Material	Plastic
Type no.	N-FAST
Info	Tinst = Tightening torque in Nm.

Standards

Technical Specification

Drill depth (min.)	55
Drill $\varnothing$	8
Effective anchorage depth (hef)	40
Grip range (tfix.max.)	30
L (mm)	75
Pull-out force (N)	560
Rivet head $\varnothing$	10
Shear load (N)	160
Tinst	4

Technical Drawing

