

MAXXFAST Anchor bolt
ThruMaxx Stainless steel A4
ETA-7 8X90



Article number	30553.080.090
Brand	-
UBB	500577357196
UNSPSC	31162101
EAN	8715494323413
PKG. of 100	Full Box Only

Technical Parameters

Diameter	8 mm
Length	90 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread

Info	Full boxes only.do = Nominal diameter of drill bits = Width across flatsring ø = Washer diameterdf = Diameter of clearance hole in the fixtureh1 = Recommended drilling depthhh(nom) = Minimum hole depthhef = Effective anchorage depthScr,N = Spacing characteristicCcr,N = Edge distance characteristicctfix(max) = Grip rangeTinst = Tightening torque in NmNrec = Recommended load in kNThe allowable load is valid for one single anchor, at non-cracked
------	---

Standards

FABORY

concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the Scr, N and Ccr, N are taken in to account. ETA-7

Technical Specification

Ccr, N	72
d-D	M8
df	9
D (mm)	8
do	8
h (nom.)	59.5
h1	65
hef	48
L (mm)	90
Nrec	5.71
Ring ø	16
s	13
Scr, N	144
tfix(max.)	20
Tinst	20

Technical Drawing

