

MAXXFAST Anchor bolt
ThruMaxx Stainless steel A4
ETA-7 10X90



Article number	30553.100.090
Brand	-
UBB	500577357352
UNSPSC	31162101
EAN	8715494323437
PKG. of 100	Full Box Only

Technical Parameters

Diameter	10 mm
Length	90 mm
Material	Stainless steel
Approval	ETA Option 7
Thread	Metric thread

Info	Full boxes only.do = Nominal diameter of drill bits = Width across flatsring $\varnothing$ = Washer diameterdf = Diameter of clearance hole in the fixtureh1 = Recommended drilling depthhh(nom) = Minimum hole depthhef = Effective anchorage depthScr,N = Spacing characteristicCcr,N = Edge distance characteristicctfix(max) = Grip rangeTinst = Tightening torque in NmNrec = Recommended load in kNThe allowable load is valid for one single anchor, at non-cracked
------	---

Standards

concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account. ETA-7

Technical Specification

Ccr, N	83
d-D	M10
df	12
D (mm)	10
do	10
h (nom.)	66.5
h1	75
hef	55
L (mm)	90
Nrec	6.35
Ring ø	20
s	17
Scr, N	165
tfix(max.)	10
Tinst	35

Technical Drawing

