



MAXXFAST Anchor bolt ThruFast - ThruMaxx Stainless steel A4 ETA-7 10X120

Article number	30553.100.120
Brand	-
UBB	500577357436
UNSPSC	31162101
EAN	8715494323444
PKG. of 50	Full Box Only

Technical Parameters

Info

do = Nominal diameter of drill bit
s = Width across flats ring \varnothing = Washer diameter
df = Diameter of clearance hole in the fixture
h1 = Recommended drilling depth
h(nom) = Minimum hole depth
hef = Effective anchorage depth
Scr,N = Spacing characteristic
Ccr,N = Edge distance characteristic
tfix(max) = Grip range
Tinst = Tightening torque in Nm
Nrec = Recommended load in kN
The allowable load is valid for one single anchor, at non-cracked concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the

Standards

	Scr, N and Ccr, N are taken in to account.
Extra info	ETA-7
Material	Stainless steel
Material technical	A4
Thread	Metric thread
Info	Full boxes only.

Technical Specification

$C_{Cr, N}$	83
Diameter (d-D)	M10
d_f	12
d_o	10
h (nom.)	66.5
h_1	75
h_{ef}	55
N_{rec}	6.35
Ring \varnothing	20
s	17
$S_{Cr, N}$	165
t_{fix} (max.)	40
T_{inst}	35

Technical Drawing

