



Self-drilling cross recessed pan head screw Phillips DIN 7504 M-H Steel Zinc plated large pack ST5,5X32MM

Article number	31820.055.032
Brand	-
UBB	500645273649
UNSPSC	31161507
EAN	8717077074132
PKG. of 500	Full Box Only

Technical Parameters

Diameter	5.5 mm
Length	32 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Pan head
Material	Steel
Surface treatment	Zinc plated
Thread	Self tapping thread
Info	Max. grip length KL = L - L1. Warning: electroplating of these products may cause hydrogen embrittlement. large pack

Standards

DIN	7504-M H
ISO	15481 H

Technical Specification

D (mm)	5.5
dk	11
k	4
L (mm)	32
L1 ≈	7
No. cross recess	3
P	1.8

Technical Drawing

