



Self-drilling cross recessed countersunk head screw Phillips DIN 7504 O- H Stainless steel A2 ST3,9X19MM

Article number	31880.039.019
Brand	-
UBB	950352877548
UNSPSC	31161507
EAN	8715492966940
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	19 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread
Info	Max. grip length KL = L - L1.

Standards

DIN	7504-O H
ISO	15482 H

Technical Specification

D (mm)	3.9
dk	7.5
L (mm)	19
L1 ≈	6
No. cross recess	2
P	1.4

Technical Drawing

