



## Plain washer with outside diameter $\approx 3 \times$ nominal thread diameter ISO 7093-1 Steel Hot dip galvanized 200 HV M12

|                |               |
|----------------|---------------|
| Article number | 38217.120.001 |
| Brand          | -             |
| UBB            | 500649076402  |
| UNSPSC         | 31161800      |
| EAN            | 8717077256064 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                   |                    |
|-------------------|--------------------|
| Diameter          | M12                |
| Class             | 200 HV             |
| For nom. size     | 12mm               |
| Material          | Steel              |
| Surface treatment | Hot dip galvanized |

### Standards

|     |        |
|-----|--------|
| ISO | 7093-1 |
|-----|--------|

### Technical Specification

|    |    |
|----|----|
| d1 | 13 |
| d2 | 37 |
| h  | 3  |

### Technical Drawing

