



**O-ring, d2=1,78MM Rubber
NBR 70° Shore A d2=1,78mm
4,76MM**

Article number	38803.004.761
Brand	-
UBB	950357180484
UNSPSC	27111900
EAN	8715492783639
PKG. of 50	Full Box Only

Technical Parameters

Diameter	4.76 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=1,78mm

Standards

Technical Specification

d1	4.76
D (mm)	4.76
Thickness	1.78

Technical Drawing

