



O-ring, d2=1,78MM Rubber NBR 70° Shore A d2=1,78mm 6,07-AS 010

Article number	38803.006.071
Brand	-
UBB	950357098157
UNSPSC	27111900
EAN	8715492783653
PKG. of 50	Full Box Only

Technical Parameters

Diameter	6.07 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=1,78mm

Standards

Technical Specification

d1	6.07
D (mm)	6.07
Thickness	1.78

Technical Drawing

