



**O-ring, d2=1,78MM Rubber
NBR 70° Shore A d2=1,78mm
15,60-AS 016**

Article number	38803.015.601
Brand	-
UBB	950357181136
UNSPSC	27111900
EAN	8715492783769
PKG. of 25	Full Box Only

Technical Parameters

Diameter	15.6 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=1,78mm

Standards

Technical Specification

d1	15.6
D (mm)	15.6
Thickness	1.78

Technical Drawing

