



O-ring, d2=1,78MM Rubber NBR 70° Shore A d2=1,78mm 20,35-AS 019

Article number	38803.020.351
Brand	-
UBB	950357181474
UNSPSC	27111900
EAN	8715492783806
PKG. of 25	Full Box Only

Technical Parameters

Diameter	20.35 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=1,78mm

Standards

Technical Specification

d1	20.35
D (mm)	20.35
Thickness	1.78

Technical Drawing

