

O-ring, d2=1,78MM Rubber NBR 70° Shore A d2=1,78mm 21,95-AS 020



Article number	38803.021.951
Brand	-
UBB	950357181540
UNSPSC	27111900
EAN	8715492783813
PKG. of 25	Full Box Only

Technical Parameters

d ₁	21.95
Diameter (mm)	21.95
Color	Black
Extra info	d2=1,78mm
Material	Rubber
Material technical	NBR 70° Shore A
Thickness	1.78

Standards

Technical Specification

Technical Drawing

