

## O-ring, d2=1,78MM Rubber NBR 70° Shore A d2=1,78mm 25,12-AS 022



Article number	38803.025.121
Brand	-
UBB	950357181706
UNSPSC	27111900
EAN	8715492783837
PKG. of 10	Full Box Only

### Technical Parameters

d <sub>1</sub>	25.12
Diameter (mm)	25.12
Color	Black
Extra info	d2=1,78mm
Material	Rubber
Material technical	NBR 70° Shore A
Thickness	1.78

### Standards

### Technical Specification

### Technical Drawing

