



O-ring, d2=2,5mm Rubber NBR 70° Shore A d2=2,5mm 11,0MM

Article number	38807.011.001
Brand	-
UBB	950357188818
UNSPSC	27111900
EAN	8715492784759
PKG. of 50	Full Box Only

Technical Parameters

Diameter	11 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=2,5mm

Standards

Technical Specification

d1	11
D (mm)	11
Thickness	2.5

Technical Drawing

