

O-ring, d2=2,62mm Rubber NBR 70° Shore A d2=2,62mm 9,92MM



Article number	38808.009.921
Brand	-
UBB	950357191523
UNSPSC	27111900
EAN	8715492785077
PKG. of 50	Full Box Only

Technical Parameters

d ₁	9.92
Diameter (mm)	9.92
Color	Black
Extra info	d2=2,62mm
Material	Rubber
Material technical	NBR 70° Shore A
Thickness	2.62

Standards

Technical Specification

Technical Drawing

