



**O-ring, d2=2,62mm Rubber
NBR 70° Shore A d2=2,62mm
10,78-AS 111**

Article number	38808.010.781
Brand	-
UBB	950357100292
UNSPSC	27111900
EAN	8715492785084
PKG. of 50	Full Box Only

Technical Parameters

Diameter	10.78 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=2,62mm

Standards

Technical Specification

d1	10.78
D (mm)	10.78
Thickness	2.62

Technical Drawing

