



O-ring, d2=2,62mm Rubber NBR 70° Shore A d2=2,62mm 12,37-AS 112

Article number	38808.012.371
Brand	-
UBB	950357100375
UNSPSC	27111900
EAN	8715492785107
PKG. of 50	Full Box Only

Technical Parameters

Diameter	12.37 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=2,62mm

Standards

Technical Specification

d1	12.37
D (mm)	12.37
Thickness	2.62

Technical Drawing

