



**O-ring, d2=2,62mm Rubber
NBR 70° Shore A d2=2,62mm
13,10MM**

Article number	38808.013.101
Brand	-
UBB	950357191861
UNSPSC	27111900
EAN	8715492785121
PKG. of 25	Full Box Only

Technical Parameters

Diameter	13.1 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=2,62mm

Standards

Technical Specification

d1	13.1
D (mm)	13.1
Thickness	2.62

Technical Drawing

