



O-ring, d2=2,62mm Rubber NBR 70° Shore A d2=2,62mm 15,08MM

Article number	38808.015.081
Brand	-
UBB	950357100524
UNSPSC	27111900
EAN	8715492785145
PKG. of 25	Full Box Only

Technical Parameters

Diameter	15.08 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=2,62mm

Standards

Technical Specification

d1	15.08
D (mm)	15.08
Thickness	2.62

Technical Drawing

