



O-ring, d2=3,53mm Rubber NBR 70° Shore A d2=3,53mm 20,22-AS 211

Article number	38812.020.221
Brand	-
UBB	950357204169
UNSPSC	27111900
EAN	8715492786500
PKG. of 10	Full Box Only

Technical Parameters

Diameter	20.22 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=3,53mm

Standards

Technical Specification

d1	20.22
D (mm)	20.22
Thickness	3.53

Technical Drawing

