



**O-ring, d2=3,53mm Rubber
NBR 70° Shore A d2=3,53mm
21,82-AS 212**

Article number	38812.021.821
Brand	-
UBB	950357204243
UNSPSC	27111900
EAN	8715492786517
PKG. of 10	Full Box Only

Technical Parameters

Diameter	21.82 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=3,53mm

Standards

Technical Specification

d1	21.82
D (mm)	21.82
Thickness	3.53

Technical Drawing

