



**O-ring, d2=3,53mm Rubber
NBR 70° Shore A d2=3,53mm
29,75-AS 217**

Article number	38812.029.751
Brand	-
UBB	950357204573
UNSPSC	27111900
EAN	8715492786579
PKG. of 10	Full Box Only

Technical Parameters

Diameter	29.75 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=3,53mm

Standards

Technical Specification

d1	29.75
D (mm)	29.75
Thickness	3.53

Technical Drawing

