



**O-ring, d2=3,53mm Rubber
NBR 70° Shore A d2=3,53mm
142,47-AS 255**

Article number	38812.142.471
Brand	-
UBB	950357210679
UNSPSC	27111900
EAN	8715492787187
PKG. of 5	Full Box Only

Technical Parameters

Diameter	142.47 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=3,53mm

Standards

Technical Specification

d1	142.47
D (mm)	142.47
Thickness	3.53

Technical Drawing

