



**O-ring, d2=4,0mm Rubber
NBR 70° Shore A d2=4,0mm
20,0MM**

Article number	38814.020.001
Brand	-
UBB	950357211826
UNSPSC	27111900
EAN	8715492787323
PKG. of 25	Full Box Only

Technical Parameters

Diameter	20 mm
Color	Black
Material	Rubber
Material technical	NBR 70° Shore A
Info	d2=4,0mm

Standards

Technical Specification

d1	20
D (mm)	20
Thickness	4

Technical Drawing

