



**O-ring, d2=5,0mm Rubber  
NBR 70° Shore A d2=5,0mm  
12,0MM**

|                |               |
|----------------|---------------|
| Article number | 38816.012.001 |
| Brand          | -             |
| UBB            | 950357214978  |
| UNSPSC         | 27111900      |
| EAN            | 8715492787699 |
| PKG. of 25     | Full Box Only |

**Technical Parameters**

|                    |                 |
|--------------------|-----------------|
| Diameter           | 12 mm           |
| Color              | Black           |
| Material           | Rubber          |
| Material technical | NBR 70° Shore A |
| Info               | d2=5,0mm        |

**Standards**

**Technical Specification**

|           |    |
|-----------|----|
| d1        | 12 |
| D (mm)    | 12 |
| Thickness | 5  |

**Technical Drawing**

