

O-ring, d2=5,0mm Rubber NBR 70° Shore A d2=5,0mm 16,0MM



Article number	38816.016.001
Brand	-
UBB	950357215132
UNSPSC	27111900
EAN	8715492787712
PKG. of 25	Full Box Only

Technical Parameters

d ₁	16
Diameter (mm)	16
Color	Black
Extra info	d2=5,0mm
Material	Rubber
Material technical	NBR 70° Shore A
Thickness	5

Standards

Technical Specification

Technical Drawing

