



**O-ring (Viton), d2=3,53mm
Rubber FPM 80° Shore
d2=3,53mm 26,57MM**

Article number	38883.026.571
Brand	-
UBB	950357430384
UNSPSC	27111900
EAN	8715492789228
PKG. of 10	Full Box Only

Technical Parameters

Diameter	26.57 mm
Color	Black
Material	Rubber
Material technical	FPM 80° Shore
Info	d2=3,53mm

Standards

Technical Specification

d1	26.57
D (mm)	26.57
Thickness	3.53

Technical Drawing

