



**Taper pin with internal thread, ground DIN 7978 A
Free-cutting steel 8X50MM**

Article number	39012.080.050
Brand	-
UBB	950359477045
UNSPSC	31163205
EAN	8715492794246
PKG. of 10	Full Box Only

Technical Parameters

Diameter	8 mm
Length	50 mm
Material	Free-cutting steel
Info	The nominal length (L, tolerance class js15) includes the rounded ends.

Standards

ISO	≈8736-A
NF	≈E27-479
NEN	≈2463
DIN	7978-A

Technical Specification

a ≈	1
d1	8
d2	5
D (mm)	8
L (mm)	50
r ≈	5
t1	8

Technical Drawing

