

Spring-type straight pin
slotted, light duty ISO 13337
Spring steel 420-560 HV30
2X20MM



Article number	39060.020.020
Brand	-
UBB	950359890114
UNSPSC	31163201
EAN	8715492794932
PKG. of 200	Full Box Only

Technical Parameters

Diameter	2 mm
Length	20 mm
Material	Spring steel
Material technical	420-560 HV30

Standards

ISO	13337
DIN	7346

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.The type of austenitic stainless spring steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506.V = minimum shear strength, double, in kN (valid for
------	--

steel pins only).The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These pins are used to connect two or more construction elements to each other.They are highly suitable to absorb shear forces.

Technical Specification

a	0.2
a (min.)	0.2
d1 (max.)	2.4
d1 (min.)	2.3
d2 ≈	1.9
D (mm)	2
L (mm)	20
s	0.2
V	1.5

Technical Drawing

