



Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 4X10MM

Article number	39090.040.010
Brand	-
UBB	500645330324
UNSPSC	31163203
EAN	8717077080034
PKG. of 100	Full Box Only

Technical Parameters

Diameter	4 mm
Length	10 mm
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

Info The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.

Standards

DIN	7979-D
ISO	≈8735-A
NEN	≈2464
NF	≈E27-475

Technical Specification

c1 ≈	0.4
c2 ≈	1.3
d1	2
D (mm)	4
L (mm)	10
L1	10
r ≈	4

Technical Drawing



