



Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 4X16MM

Article number	39090.040.016
Brand	-
UBB	500645330571
UNSPSC	31163203
EAN	8717077080058
PKG. of 100	Full Box Only

Technical Parameters

Diameter	4 mm
Length	16 mm
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

Info The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.

Standards

NEN	≈2464
ISO	≈8735-A
DIN	7979-D
NF	≈E27-475

Technical Specification

c1 ≈	0.4
c2 ≈	1.3
d1	2
D (mm)	4
L (mm)	16
L1	16
r ≈	4

Technical Drawing



