

## Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 5X10MM



Article number	39090.050.010
Brand	-
UBB	500501654015
UNSPSC	31163203
EAN	8715494262514
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (mm)	5
L <sub>1</sub>	10
Info	The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.
Length (L) (mm)	10
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

### Standards

DIN	7979 D
NF	E27-475
ISO	8735 A

### Technical Specification

c <sub>1</sub> ≈	0.5
c <sub>2</sub> ≈	1.7
d <sub>1</sub>	M3
r ≈	5
t <sub>1</sub>	6

### Technical Drawing

