

## Parallel pin (dowel pin) with internal thread, hardened, ground DIN 7979 D Steel 60±2HRC Plain 5X14MM



Article number	39090.050.014
Brand	-
UBB	500645330811
UNSPSC	31163203
EAN	8717077080089
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (mm)	5
L <sub>1</sub>	14
Info	The tolerance class of outer diameter d is m6. The nominal length (L tolerance class js15) includes the rounded ends. Shank with slight flat or small groove at the manufacturers discretion.
Length (L) (mm)	14
Material	Steel
Material technical	60±2HRC
Surface treatment	Plain

### Standards

NF	E27-475
DIN	7979 D
ISO	8735 A

### Technical Specification

c <sub>1</sub> ≈	0.5
c <sub>2</sub> ≈	1.7
d <sub>1</sub>	M3
r ≈	5
t <sub>1</sub>	6

### Technical Drawing

