


Spring-type straight pin
slotted, heavy duty ISO 8752
Spring steel 420-560 HV30
1X6MM



Article number	39100.010.006
Brand	-
UBB	950359345044
UNSPSC	31163201
EAN	8715492802033
PKG. of 200	Full Box Only

Technical Parameters

Diameter	1 mm
Length	6 mm
Material	Spring steel
Material technical	420-560 HV30

Standards

DIN	1481
ISO	8752
NEN	2458
BS	7060

Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These
------	---

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technical Specification

a (min.)	0.15
d1 (max.)	1.3
d1 (min.)	1.2
d2 ≈	0.8
D (mm)	1
L (mm)	6
s	0.2
V	0.7

Technical Drawing

