


Spring-type straight pin slotted, heavy duty ISO 8752 Spring steel 420-560 HV30 25X32MM



Article number	39100.250.032
Brand	-
UBB	500644943341
UNSPSC	31163201
EAN	8717077043824
PKG. of 10	Full Box Only

Technical Parameters

Diameter	25 mm
Length	32 mm
Material	Spring steel
Material technical	420-560 HV30

Standards

DIN	1481
NEN	2458
BS	7060
ISO	8752

Info	Warning: electroplating of these products may cause hydrogen embrittlement. Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These
------	---

pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

Technical Specification

a (min.)	3
d1 (max.)	25.9
d1 (min.)	25.5
d2 ≈	15.5
D (mm)	25
L (mm)	32
s	5
V	438.5

Technical Drawing

