


## Spring-type straight pin slotted, heavy duty ISO 8752 Spring steel 420-560 HV30 Zinc plated 4X10MM



Article number	39105.040.010
Brand	-
UBB	500649080107
UNSPSC	31163201
EAN	8717077256439
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	4 mm
Length	10 mm
Material	Spring steel
Material technical	420-560 HV30
Surface treatment	Zinc plated

### Standards

BS	7060
ISO	8752
NEN	2458
DIN	1481

Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter  $d \geq 10$  mm a single chamfer configuration is optional at the discretion of the manufacturer. V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction

elements to each other. They are highly suitable to absorb shear forces. If these pins are employed with bolted joints the below arrangement should be used:

## Technical Specification

a (min.)	0.65
d1 (max.)	4.6
d1 (min.)	4.4
d2 ≈	2.8
D (mm)	4
L (mm)	10
s	0.8
V	11.24

## Technical Drawing

